



Close Couple Suites (All measurements in mm)														
Model	Number	A Cistern (Width)	B Pan (Width)	C Suite (Length)	D Cistern (Depth)	E Unit (Height)	F Uni Trap Centre	G Wall To Spigot	H Water Inlet from cistern centre	I Water Inlet (Height)	J Pan (Height)	K Trap Dia	L Standard Outlet Set out Range OK-3302	L Alternative Outlet Set out Range Note 2 (MTJT34)
ALTO	OK-0231	380	365	675	165	770	180	185	110	680	390	100	65-150	180-210
ALTO PEDESTAL PAN	OK-0235	-	365	520	-	-	180	30	-	-	390	100	-	80
BOLLO	OK-0002	390	370	720	185	835	185	230	85	760	400	100	65-190	180-260
CAL	OK-0150	365	360	700	185	850	185	210	127	790	390	105	65-180	180-270
CAL PEDESTAL PAN	OK-0155	-	360	520	-	-	185	50	-	-	390	100	-	80
ECO	OK-21108	380	360	670	170	795	N/A	N/A	Right hand	Bottom	390	100	195 <i>Note 1</i>	n/a
FLUID	OK-0180	360	360	630	160	780	190	175	90	715	390	100	65-140	160-210
FLUID PEDESTAL PAN	OK-0185	-	360	520	-	-	190	70	-	-	390	100	-	80
LIBERTY Bottom inlet	OK-0190	355	380	690	185	805	190	215	Right or Left hand	Bottom	400	100	65-160	180-240
LIBERTY Back inlet	OK-0190 BK	355	380	690	185	805	190	215	120	745	400	100	65-160	180-240
LIBERTY PEDESTAL PAN	OK-0195	-	380	550	-	-	190	20	-	-	400	100	-	80
REO 45 & REO	OK-0140.45	385	385	695	160	760	185	175	Right hand	Bottom	380	100	65-160	180-240
RETTANGOLO MKII	OK-0014.1	390	385	710	170	845	185	215	85	765	400	100	65-175	180-210
DIFFERENTE Discontinued	OK-0213	365	350	695	180	895	185	200	127	840	400	100	65-160	180-260
BASSO Discontinued	OK-0023	300	420	720	180	805	180	220	0	760	400	100	65-185	n/a
CONO Discontinued	OK-0792	230	400	740	175	835	180	230	0	770	390	100	65-185	n/a
RETTANGOLO Discontinued	OK-0014	270	380	720	170	850	180	190	0	780	405	100	65-140	n/a

Note 1: Not recommended to be installed where an offset pan collar exceeding 25mm is required.
Note 2: Alternative outlet bend at extra charge.

Current
Available soon
Discontinued

Updated: 6/07/2011